

## Product data sheet

### Characteristics

# PDL860M16PBWH

## 1-Way Half Standard Press Switch Module;16A/16AX, 1P, Unprinted Legend,White



### Main

Range of product	Modena 800 Series
Product or component type	Switch module
Control type	Rocker
Colour tint	White
Quantity per set	Set of 20
Type of packing	Carton

### Complementary

Material	PC (polycarbonate)
Surface finish	Matt
Installation direction	Vertical Horizontal
Width	12.4 mm
Height	45.5 mm
Depth	21.45 mm
Rated current	16 AX 16 A
[Ue] rated operational voltage	250 V
Network type	AC
Network number of phases	1 phase
Mounting mode	Front
Cable composition	6 x 1.5 mm <sup>2</sup> 2 x 4 mm <sup>2</sup> 3 x 2.5 mm <sup>2</sup> 9 x 1 mm <sup>2</sup>
Connector type	#1 Square Head/#2 Phillips Screw
Auxiliary contact composition	1 NO

### Packing Units

Package 1 Weight	17.000 kg
Package 1 Height	42.000 mm
Package 1 width	13.000 mm
Package 1 Length	46.000 mm

### Offer Sustainability

EU RoHS Directive	Under investigation
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>