

## Product data sheet

### Characteristics

# PDL861M16OWH

## 2-Way Half Standard Printed Switch Module; 16A/16AX, 1P, OSD LIGHT Legend, White



### Main

Range of product	Modena 800 Series
Product or component type	Switch module
Control type	Rocker
Colour tint	White
Quantity per set	Set of 20
Type of packing	Carton

### Complementary

Material	PC (polycarbonate)
Surface finish	Matt
Installation direction	Horizontal Vertical
Length	44.8 mm
Width	12.3 mm
Rated current	16 AX 16 A
[Ue] rated operational voltage	250 V
Network type	AC
Network number of phases	1 phase
Marking	OUTSIDE LIGHT
Mounting mode	Front
Cable composition	9 x 1 mm <sup>2</sup> 2 x 4 mm <sup>2</sup> 6 x 1.5 mm <sup>2</sup> 3 x 2.5 mm <sup>2</sup>
Connector type	#1 Square Head/#2 Phillips Screw

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.2 cm
Package 1 Width	1.3 cm
Package 1 Length	4.6 cm
Package 1 Weight	17 g

### Offer Sustainability

EU RoHS Directive	Under investigation
Circularity Profile	No need of specific recycling operations