

## Product data sheet

### Characteristics

# PDL880MT1SPBWH

## Push Button Switch Module with Optional Blue LED; 10A/10AX/M50, 1-Gang, 1P, White



### Main

Range of product	Modena 800 Series
Product or component type	Switch module
Control type	Push-button
Colour tint	White
Quantity per set	Set of 5
Type of packing	Carton



### Complementary

Material	PC (polycarbonate)
Surface finish	Matt
Installation direction	Vertical Horizontal
Width	25 mm
Height	45 mm
Rated current	10 A 10 AX
[Ue] rated operational voltage	250 V
Network type	AC
Network number of phases	1 phase
Number of gangs	1 gang
Mounting mode	Front
Connector type	#1 Square Head/#2 Phillips Screw
Auxiliary contact composition	1 NO/NC

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.95 cm
Package 1 Width	2.55 cm
Package 1 Length	4.51 cm
Package 1 Weight	0.027 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>

