

Product data sheet

Characteristics

PDL881VWH

2-Way Vertical Switch With Grid And Clip ; 16A/16AX, 1-Gang, White



Main

Range of product	Modena 800 Series
Product or component type	Switch module
Control type	Rocker
Colour tint	White
Quantity per set	Set of 10
Type of packing	Carton

Complementary

Material	PC (polycarbonate)
Surface finish	Glossy and matt
Installation direction	Vertical
Width	85 mm
Height	124 mm
Rated current	16 A 16 AX
[Ue] rated operational voltage	250 V
Network type	AC
Network number of phases	1 phase
Number of gangs	1 gang
Mounting mode	Surface mounted
Fixing center	84 mm
Cable composition	2 x 4 mm ² 9 x 1 mm ² 3 x 2.5 mm ² 6 x 1.5 mm ²
Connector type	#1 Square Head/#2 Phillips Screw

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.5 cm
Package 1 Width	4.33 cm
Package 1 Length	12 cm
Package 1 Weight	0.11 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations