

## Product data sheet

### Characteristics

# PDL882PBWH

2-Way Push Button Switch With Grid & Clip ;  
16A/16AX/10A, 22-Gang, 1P, White

### Main

Range of product	Modena 800 Series
Product or component type	Switch module
Control type	Push-button
Colour tint	White
Quantity per set	Set of 10
Type of packing	Carton

### Complementary

Material	PC (polycarbonate)
Surface finish	Matt
Installation direction	Horizontal
Width	124 mm
Height	85 mm
Depth	9 mm
Rated current	16 AX 10 A 16 A
[Ue] rated operational voltage	250 V 24 V
Network type	AC
Network number of phases	1 phase
Number of gangs	2 gangs
Mounting mode	Surface mounted
Fixing center	84 mm
Connector type	#1 Square Head/#2 Phillips Screw

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.03 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.