

Product data sheet

Characteristics

PDL882WH

2-Way Switch With Grid and Clip ; 16A/16AX, 2-Gang, 1P, White

Main

Range of product	Modena 800 Series
Product or component type	Switch module
Control type	Rocker
Colour tint	White
Quantity per set	Set of 10
Type of packing	Carton




Complementary

Material	PC (polycarbonate)
Surface finish	Matt
Installation direction	Horizontal
Width	124 mm
Height	85 mm
Depth	9 mm
Rated current	16 A 16 AX
[Ue] rated operational voltage	250 V
Network type	AC
Network number of phases	1 phase
Number of gangs	2 gangs
Mounting mode	Surface mounted
Fixing center	84 mm
Connector type	#1 Square Head/#2 Phillips Screw

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5 cm
Package 1 Width	9 cm
Package 1 Length	12.5 cm
Package 1 Weight	110 g

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes