

# Product data sheet

## Characteristics

# PDL883VWH

## 2-Way Vertical Switch With Grid And Clip ; 16A/16AX, 3-Gang, White



### Main

Range of product	Modena 800 Series
Product or component type	Switch module
Control type	Rocker
Colour tint	White
Quantity per set	Set of 10
Type of packing	Carton


### Complementary

Material	PC (polycarbonate)
Surface finish	Glossy and matt
Installation direction	Vertical
Width	85 mm
Height	124 mm
Depth	9 mm
Rated current	16 A 16 AX
[Ue] rated operational voltage	250 V
Network type	AC
Network number of phases	1 phase
Number of gangs	3 gangs
Mounting mode	Surface mounted
Fixing center	84 mm
Connector type	#2 Phillips/Slot Screw

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5 cm
Package 1 Width	8.5 cm
Package 1 Length	12.5 cm
Package 1 Weight	0.119 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 Yes

