

## Product data sheet

### Characteristics

# PDL892ABLWH

## Double Vertical Switch Socket Module With Blue Led; 10A, 2-Gang



### Main

Range of product	Modena 800 Series
Product or component type	Switched socket
Quantity per set	Set of 10
Type of packing	Carton
Colour tint	White



### Complementary

Material	PC (polycarbonate)
Surface finish	Glossy and matt
Installation direction	Vertical
Width	85 mm
Height	124 mm
Depth	9 mm
Rated current	10 A
[Ue] rated operational voltage	250 V
Network frequency	50 Hz
Network number of phases	1 phase
Number of gangs	2 gangs
Mounting mode	Surface mounted
Fixing center	84 mm

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4 cm
Package 1 Width	8.5 cm
Package 1 Length	12.5 cm
Package 1 Weight	0.11 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 Yes

