

Product data sheet

Characteristics

PDL892AWH

Double Vertical Switch Socket Module With Blue LED; 10A, 2-Gang, White



Main

Range of product	Modena 800 Series
Product or component type	Switched socket
Quantity per set	Set of 10
Type of packing	Carton
Colour tint	White


Complementary

Material	PC (polycarbonate)
Surface finish	Glossy and matt
Installation direction	Vertical
Width	85 mm
Height	124 mm
Depth	9 mm
Rated current	10 A
[Ue] rated operational voltage	250 V
Network frequency	50 Hz
Network number of phases	1 phase
Number of gangs	2 gangs
Mounting mode	Surface mounted
Fixing center	84 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	8.5 cm
Package 1 Length	12.5 cm
Package 1 Weight	0.11 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

