

Product data sheet

Characteristics

PDL892MAWH

Double Vertical Integrally Switched Socket Module; 10A, 250VAC, 2-Gang, White



Main

| | |
|---------------------------|-------------------|
| Range of product | Modena 800 Series |
| Product or component type | Switched socket |
| Quantity per set | Set of 10 |
| Type of packing | Carton |
| Colour tint | White |

Complementary

| | |
|--------------------------------|--------------------|
| Material | PC (polycarbonate) |
| Surface finish | Matt |
| Installation direction | Vertical |
| Width | 44.7 mm |
| Height | 74.8 mm |
| Rated current | 10 A |
| [Ue] rated operational voltage | 250 V |
| Network frequency | 50 Hz |
| Network number of phases | 1 phase |
| Number of gangs | 2 gangs |
| Mounting mode | Front |

Packing Units

| | |
|------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 3.5 cm |
| Package 1 Width | 4.5 cm |
| Package 1 Length | 7.5 cm |
| Package 1 Weight | 0.059 kg |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| EU RoHS Directive | Compliant with Exemptions |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |