

Product data sheet

Characteristics

PDL895ABLWH

Single Horizontal Switch Socket Module With Blue LED; 10A, 2-Gang, White

Main

| | |
|---------------------------|-------------------|
| Range of product | Modena 800 Series |
| Product or component type | Switched socket |
| Quantity per set | Set of 10 |
| Type of packing | Carton |
| Colour tint | White |



Complementary

| | |
|--------------------------------|--------------------|
| Material | PC (polycarbonate) |
| Surface finish | Glossy and matt |
| Installation direction | Horizontal |
| Width | 124 mm |
| Height | 85 mm |
| Depth | 9 mm |
| Rated current | 10 A |
| [Ue] rated operational voltage | 250 V |
| Network frequency | 50 Hz |
| Network number of phases | 1 phase |
| Number of gangs | 2 gangs |
| Mounting mode | Surface mounted |
| Fixing center | 84 mm |

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 3 cm |
| Package 1 Width | 8.5 cm |
| Package 1 Length | 12.5 cm |
| Package 1 Weight | 114 g |

Offer Sustainability

| | |
|----------------------------|---|
| EU RoHS Directive | Compliant with Exemptions |
| Mercury free | Yes |
| RoHS exemption information |  Yes |
| China RoHS Regulation |  China RoHS Declaration |
| Environmental Disclosure |  Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |