

Product data sheet

Characteristics

PDL895AWH

Fully Assembled Single Horizontal Switch Socket Module; 10A, 2-Gang, White



Main

Range of product	Modena 800 Series
Product or component type	Switched socket
Quantity per set	Set of 10
Type of packing	Carton
Colour tint	White




Complementary

Material	PC (polycarbonate)
Surface finish	Glossy and matt
Installation direction	Horizontal
Width	124 mm
Height	85 mm
Depth	9 mm
Rated current	10 A
[Ue] rated operational voltage	250 V
Network frequency	50 Hz
Network number of phases	1 phase
Number of gangs	2 gangs
Mounting mode	Surface mounted
Fixing center	84 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.114 kg
Package 1 Height	3.5 cm
Package 1 width	9 cm
Package 1 Length	12.5 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes

China RoHS Regulation

 [China RoHS Declaration](#)

Environmental Disclosure

 [Product Environmental Profile](#)
