

Product data sheet

Characteristics

PDL901/15WH

Side Entry 3Pin Rewirable Heavy Duty Plug; 15A, White

Main

Range of product	900 Series
Product or component type	Plug
Material	PC (polycarbonate)
Colour tint	White

Complementary

Surface finish	Gloss
Width	45 mm
Diameter	45 mm
Rated current	15 A
[Ue] rated operational voltage	230/240 V
Network frequency	50 Hz
Pin number	3
Ambient air temperature for operation	-10...40 °C
Cable cross section	0.75...1.5 mm ²
Connector type	Screw terminals
Quantity per set	Set of 20
Type of packing	Carton

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	4.5 cm
Package 1 Length	5.5 cm
Package 1 Weight	0.032 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	400
Package 2 Height	21.6 cm
Package 2 Width	32.5 cm
Package 2 Length	62.9 cm
Package 2 Weight	17300.0 g
Unit Type of Package 3	PAL
Number of Units in Package 3	4800
Package 3 Height	140 cm
Package 3 Width	114 cm
Package 3 Length	114 cm
Package 3 Weight	153.6 kg

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes