

Product data sheet

Characteristics

PDL901WH

Side Entry 3Pin Rewirable Heavy Duty Plug; 10A, White

Main

Range of product	900 Series
Product or component type	Plug
Material	PC (polycarbonate)
Colour tint	White

Complementary

Surface finish	Gloss
Width	45 mm
Diameter	45 mm
Rated current	10 A
[Ue] rated operational voltage	230/240 V
Network frequency	50 Hz
Pin number	3
Ambient air temperature for operation	-10...40 °C
Cable cross section	0.75...1.5 mm ²
Connector type	Screw terminals
Quantity per set	Set of 20
Type of packing	Carton

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	4.5 cm
Package 1 Length	5.5 cm
Package 1 Weight	0.031 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	20
Package 2 Height	76 cm
Package 2 Width	118 cm
Package 2 Length	193 cm
Package 2 Weight	0.74 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes