

Product data sheet

Characteristics

PDL905WH

Back Entry Rewirable Heavy Duty Plug; 10A, White



Main

Range of product	900 Series
Product or component type	Plug
Material	PC (polycarbonate)
Colour tint	White

Complementary

Surface finish	Gloss
Width	45 mm
Diameter	45 mm
Rated current	10 A
[Ue] rated operational voltage	230/240 V
Network frequency	50 Hz
Pin number	3
Ambient air temperature for operation	-10...40 °C
Cable cross section	0.75...1.5 mm ²
Connector type	Screw terminals
Quantity per set	Set of 20
Type of packing	Carton

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	4.5 cm
Package 1 Length	6 cm
Package 1 Weight	0.038 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	200
Package 2 Height	21 cm
Package 2 Width	31 cm
Package 2 Length	50 cm
Package 2 Weight	10100.0 g
Unit Type of Package 3	PAL
Number of Units in Package 3	4000
Package 3 Height	140 cm
Package 3 Width	114 cm

Package 3 Length	114 cm
Package 3 Weight	152.0 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations