

Product data sheet

Characteristics

PDLDBF60

DBF Series 60-Way Distribution Board; 100A, Flush Mount, Plastic, Light Grey



Main

Range of product	Superboard Series
Product or component type	Distribution board
Material	ABS (acrylonitrile butadiene-styrene)
Colour tint	Light grey
Surface finish	Gloss

Complementary

Installation direction	Vertical
Width	376 mm
Height	800 mm
Depth	100 mm
Rated current	100 A
[Ue] rated operational voltage	415 V
[Ui] rated insulation voltage	1000 V
Mounting mode	Flush-mounted
Cable cross section	25 mm ²
Cut-out dimensions	335 x 765 x 80 mm
Quantity per set	Set of 1
Type of packing	Carton

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.0 cm
Package 1 Width	38.0 cm
Package 1 Length	82.0 cm
Package 1 Weight	6.649 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

