

## Product data sheet

### Characteristics

# PDLO394-BK

## Outdoor Socket Switch, Weathershield, Horizontal Single 10A 250V



### Main

Range of product	Iconic
Range	Iconic
Product or component type	Switched socket
Device presentation	Complete product
Product brand	PDL
Outlet poles configuration	1P + E
Outlet standard	Australian
Switch application	On/off switching

### Complementary

Socket-outlet type	Single socket-outlet
Control type	Rocker
Device mounting	Wall mounted
Mounting position	Horizontal
Number of power socket outlets	1
Number of rocker	1
Range compatibility	Iconic
Outlet standard description	With earthing contact
Outlet standard deviation	Australian/New Zealand
Pin number	3
Fixing mode	By screw
Installation direction	Horizontal
Surface finish	Matt
Type of packing	Box
Sale per indivisible quantity	1
Rated current	10 A at 250 V AC 50 Hz
Electrical durability	12000 cycles
Connections - terminals	3 screw terminals
Screwdriver shape	Square drive no 1 (SQ1) Philips No 2
Clamping connection capacity	3 x 2.5 mm <sup>2</sup> 2 x 4 mm <sup>2</sup>
Wire stripping length	16 mm
Material	PC (polycarbonate) ABS (acrylonitrile butadiene-styrene) POM (polyoxymethylene)
Type of installation	Outdoor
Height	85 mm
Width	115.5 mm
Depth	70 mm
Net weight	0.22 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Environment

Ambient air temperature for storage	0...60 °C
Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %
Standards	AS/NZS 3112
Product certifications	RCM
IP degree of protection	IP54

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.7 cm
Package 1 Width	11.9 cm
Package 1 Length	8.9 cm
Package 1 Weight	274.0 g
Unit Type of Package 2	BB2
Number of Units in Package 2	30
Package 2 Height	30.9 cm
Package 2 Width	41.3 cm
Package 2 Length	45.9 cm
Package 2 Weight	9.22 kg
Unit Type of Package 3	P06
Number of Units in Package 3	360
Package 3 Height	105.0 cm
Package 3 Width	60.0 cm
Package 3 Length	80.0 cm
Package 3 Weight	119.14 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
Halogen content performance	Halogen free plastic parts product