

Product data sheet

Characteristics

PDLP300ALEDB-BK

LED Module Pro Series, Bright white lighting, With Black rocker, 250 V, Black



Main

Range of product	Pro Series
Product or component type	LED Rocker
Device presentation	Basic element
Colour	Black (BK)
Type of packing	Polybag
Quantity per set	10
Sale per indivisible quantity	10
Load type	240 V AC
Light source	LED 60 mW

Complementary

Device mounting	Flush
Control type	Rocker
Number of rocker	1
Actuator	Rocker Dolly
Product destination	Switch
Range compatibility	Pro Series Iconic
Fixing mode	Clip-in
Surface finish	Matt
Surface treatment	Untreated
Rated current	0.002 mA at 250 V AC 50 Hz
Connections - terminals	Flying leads
Local signalling	White indicator white for indicator
Material	ABS (acrylonitrile butadiene-styrene): rocker
Height	23 mm
Width	23 mm
Depth	32 mm
Net weight	0.01 kg

Environment

Ambient air temperature for operation	0...45 °C
Ambient air temperature for storage	0...45 °C
Relative humidity	10...95 %
Environmental characteristic	UV resistant indoor use

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.9 cm
Package 1 Width	1.8 cm
Package 1 Length	2.3 cm
Package 1 Weight	3.78 g

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------