

Product data sheet

Characteristics

PDLP343H-XW

Pro Series, Cover Plate USB Charger, Type A, 2.1A 3-Gang, White



Main

| | |
|---|--|
| Range | Pro Series |
| Product or component type | USB charger |
| [Ue] rated operational voltage | 220/240 V AC 50 Hz |
| Integrated connection type | 3 USB 2.0 type A 5 V DC, maximum load current: 2.1 A |
| Maximum load current with 2 outputs used simultaneously | 4.5 A |

Complementary

| | |
|---------------------------------------|--|
| Device mounting | Flush |
| Device presentation | Complete product |
| Colour tint | White (XW) |
| Surface finish | Matt Textured |
| Fixing mode | By screws |
| Type of packing | Polybag |
| Quantity per set | Set of 5 |
| Ambient air temperature for operation | 0...45 °C |
| Ambient air temperature for storage | -5...50 °C |
| Relative humidity | 10...95 % |
| Material | PC (polycarbonate) PP (polypropylene) ABS (acrylonitrile butadiene-styrene) |
| Protection type | Short time short-circuit protection |
| Number of terminals | 3 screw terminal |
| Screwdriver shape | Square drive no 1 (SQ1) Philips No 2 |
| Clamping connection capacity | 1 x 2.5...4 x 2.5 mm ² for rigid or stranded cable(s) 3 x 4 mm ² for rigid or stranded cable(s) |
| Wire stripping length | 16 mm |
| Standards | AS/NZ 3112 |
| Height | 78 mm |
| Width | 38 mm |
| Depth | 38 mm |
| Embedding depth | 35 mm |
| Net weight | 0.094 kg |

Environment

| | |
|-----------------------------|----------|
| Product certifications | RCM |
| Electrical insulation class | Class II |
| IK degree of protection | IK08 |
| IP degree of protection | IP21 |

Packing Units

| | |
|------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 3.8 cm |
| Package 1 Width | 7.8 cm |
| Package 1 Length | 11.6 cm |
| Package 1 Weight | 102.53 g |

Offer Sustainability

| | |
|----------------------------|--|
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Compliant with Exemptions |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |