

Product data sheet

Characteristics

PDLP351-XW

Pro Series, Switch + PCU Unit, 20A 16AX 1/2-Way Vertical, White



Main

Range	Pro Series
Product or component type	Switch
Colour tint	White
Type of packing	Polybag
Quantity per set	Set of 10

Complementary

Device presentation	Complete product
Control type	Rocker
Device mounting	Wall
Installation direction	Vertical
Switch function	1-pole 1/2-way
Number of rocker	1
Rated current	20 A/16 AX
[Ue] rated operational voltage	230/240 V
Material	PC (polycarbonate) PP (polypropylene) ABS (acrylonitrile butadiene-styrene) PA66 POM (polyoxymethylene)
Fixing mode	By screws
Surface finish	Glossy
Surface treatment	Untreated
Connections - terminals	Screw terminal
Clamping connection capacity	1 x 1.5...4 x 1.5 mm ² for rigid or stranded cable(s) 3 x 2.5 mm ² for stranded cable(s) 1 x 4 mm ² for stranded cable(s)
Height	116 mm
Width	72 mm
Depth	21 mm
Net weight	0.074 kg

Environment

Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %
Product certifications	RCM

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.0 cm
Package 1 Width	7.8 cm
Package 1 Length	11.6 cm
Package 1 Weight	43.53 g

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------