

Product data sheet

Characteristics

PDLP361-BK

Pro Series, Switch, Architrave 1/2-Way 20A 16AX 1-Gang, Black



Main

Range	Pro Series
Product or component type	Switch
Colour tint	Black
Type of packing	Polybag
Quantity per set	Set of 10

Complementary

Device presentation	Complete product
Control type	Rocker
Device mounting	Wall
Installation direction	Vertical
Switch function	1-pole 1/2-way
Number of rocker	1
Rated current	20 A/16 AX
[Ue] rated operational voltage	230/240 V
Material	PC (polycarbonate) PP (polypropylene) ABS (acrylonitrile butadiene-styrene) POM (polyoxymethylene)
Fixing mode	By screws
Surface finish	Glossy
Surface treatment	Untreated
Connections - terminals	Screw terminal
Clamping connection capacity	1 x 1.5...4 x 1.5 mm ² for rigid or stranded cable(s) 3 x 2.5 mm ² for stranded cable(s) 1 x 4 mm ² for stranded cable(s)
Height	113 mm
Width	38 mm
Depth	40 mm
Net weight	0.048 kg

Environment

Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %
Product certifications	RCM

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.8 cm
Package 1 Width	7.8 cm
Package 1 Length	11.6 cm
Package 1 Weight	52.33 g

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------