

## Product data sheet

### Characteristics

# PDLP380ALR-XW

## Pro Series, Dolly Rocker, Latch, White



### Main

Range	Pro Series
Product or component type	Switch
Device application	Latched control
Colour tint	White
Type of packing	Polybag
Quantity per set	Set of 20

### Complementary

Device presentation	Mechanism with central plate
Control type	Rocker
Switch function	2 positions
[Ue] rated operational voltage	250 V
Material	PC (polycarbonate) PA66 ABS (acrylonitrile butadiene-styrene)
Fixing mode	By clips
Surface finish	Glossy
Surface treatment	Untreated
Connections - terminals	Screw terminal
Clamping connection capacity	1 x 1.5...4 x 1.5 mm <sup>2</sup> for rigid or stranded cable(s) 3 x 2.5 mm <sup>2</sup> for stranded cable(s) 1 x 4 mm <sup>2</sup> for stranded cable(s)
Height	23 mm
Width	23 mm
Depth	33 mm
Net weight	0.016 kg

### Environment

Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.9 cm
Package 1 Width	1.8 cm
Package 1 Length	2.3 cm
Package 1 Weight	18.0 g

### Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------