

Product data sheet

Characteristics

PDLP380ALRSENSOR-XW

Pro Series, latching switch, 2 positions, marked SENSOR, White



Main

Range	Pro Series
Product or component type	Switch
Device application	Latched control
Colour tint	White
Type of packing	Polybag
Quantity per set	Set of 20

Complementary

Device presentation	Mechanism with central plate
Control type	Rocker
Switch function	2 positions
Marking	Sensor
Material	PC (polycarbonate) PA66 ABS (acrylonitrile butadiene-styrene)
Fixing mode	By clips
Surface finish	Glossy
Surface treatment	Untreated
Connections - terminals	Screw terminal
Clamping connection capacity	1 x 1.5...4 x 1.5 mm ² for rigid or stranded cable(s) 3 x 2.5 mm ² for stranded cable(s) 1 x 4 mm ² for stranded cable(s)
Height	23 mm
Width	23 mm
Depth	32 mm
Net weight	0.016 kg

Environment

Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.9 cm
Package 1 Width	1.8 cm
Package 1 Length	2.3 cm
Package 1 Weight	18.0 g

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------