

Product data sheet

Characteristics

PDLP380M32HOB-XW

Pro Series, switch, 300M, marked HOB, 32 A, White



Main

Range	Pro Series
Product or component type	Switch
Provided equipment	Rocker
Colour tint	White
Type of packing	Polybag
Quantity per set	Set of 10

Complementary

Device presentation	Mechanism with central plate
Control type	Rocker
Switch function	1-pole 1-way
Marking	Hob
Rated current	32 A
[Ue] rated operational voltage	250 V
Material	PC (polycarbonate) PA66 ABS (acrylonitrile butadiene-styrene)
Fixing mode	By clips
Surface finish	Glossy
Surface treatment	Untreated
Connections - terminals	Screw terminal
Clamping connection capacity	1 x 1.5...4 x 1.5 mm ² for rigid or stranded cable(s) 3 x 2.5 mm ² for stranded cable(s) 1 x 4 mm ² for stranded cable(s)
Height	23 mm
Width	23 mm
Depth	32 mm
Net weight	0.016 kg

Environment

Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %
Product certifications	RCM

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.2 cm
Package 1 Width	2.2 cm
Package 1 Length	2.4 cm
Package 1 Weight	20.98 g

