

## Product data sheet

### Characteristics

# PDLP380M32O-XW

Pro Series, switch, 300M, marked OVEN, 32 A, White



### Main

Range	Pro Series
Product or component type	Switch
Provided equipment	Rocker
Colour tint	White
Type of packing	Polybag
Quantity per set	Set of 10

### Complementary

Device presentation	Mechanism with central plate
Control type	Rocker
Switch function	1-pole 1-way
Marking	Oven
Rated current	32 A
[Ue] rated operational voltage	250 V
Material	PC (polycarbonate) PA66 ABS (acrylonitrile butadiene-styrene)
Fixing mode	By clips
Surface finish	Glossy
Surface treatment	Untreated
Connections - terminals	Screw terminal
Clamping connection capacity	1 x 1.5...4 x 1.5 mm <sup>2</sup> for rigid or stranded cable(s) 3 x 2.5 mm <sup>2</sup> for stranded cable(s) 1 x 4 mm <sup>2</sup> for stranded cable(s)
Height	23 mm
Width	23 mm
Depth	32 mm
Net weight	0.01 kg

### Environment

Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %
Product certifications	RCM

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.2 cm
Package 1 Width	2.2 cm
Package 1 Length	2.4 cm
Package 1 Weight	20.98 g

