

Product data sheet

Characteristics

PDLP382-XW

Pro Series, 2 switches, vertical, 1 or 2 way, 20 A / 16 AX, White



Main

Range	Pro Series
Product or component type	Switch
Device application	Lighting
Colour tint	White
Type of packing	Polybag
Quantity per set	Set of 10

Complementary

Device presentation	Complete product
Control type	Rocker
Device mounting	Wall
Installation direction	Vertical
Switch function	1-pole 1/2-way
Number of rocker	2
Rated current	20 A/16 AX
[Ue] rated operational voltage	250 V
Material	PC (polycarbonate) PP (polypropylene) ABS (acrylonitrile butadiene-styrene) POM (polyoxymethylene)
Fixing mode	By screws
Surface finish	Glossy
Surface treatment	Untreated
Connections - terminals	Screw terminal
Clamping connection capacity	1 x 1.5...4 x 1.5 mm ² for rigid or stranded cable(s) 3 x 2.5 mm ² for stranded cable(s) 1 x 4 mm ² for stranded cable(s)
Height	116 mm
Width	78 mm
Depth	38 mm
Net weight	0.082 kg

Environment

Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %
Product certifications	RCM

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------