

Product data sheet

Characteristics

PDLP382C-BK

Pro Series, Cover Plate Switch, 20A 2-Gang, Black



Main

Range	Pro Series
Product or component type	Cover frame
Colour tint	Black (BK)
Type of packing	Polybag

Complementary

Range compatibility	Pro Series switch
Product destination	Switch
Number of rocker	2
Installation direction	Vertical
Fixing mode	Clip-on
Surface finish	Glossy
Material	PC (polycarbonate): window ABS (acrylonitrile butadiene-styrene): skin
Height	116 mm
Width	78 mm
Depth	9 mm
Net weight	0.018 kg


Environment

Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.9 cm
Package 1 Width	7.8 cm
Package 1 Length	11.6 cm
Package 1 Weight	19.94 g

Offer Sustainability

EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.