

Product data sheet

Characteristics

PDLP387M3T-XW

Pro Series, Module Toggle Switch, 10A 3-Positions, White



Main

| | |
|---------------------------|------------|
| Range | Pro Series |
| Product or component type | Switch |
| Colour tint | White |
| Type of packing | Polybag |
| Quantity per set | Set of 20 |

Complementary

| | |
|--------------------------------|--|
| Device presentation | Mechanism with central plate |
| Control type | Rocker |
| Switch function | 3 positions |
| Rated current | 10 A |
| [Ue] rated operational voltage | 250 V |
| Material | PC (polycarbonate) PA66 ABS (acrylonitrile butadiene-styrene) |
| Fixing mode | By clips |
| Surface finish | Glossy |
| Surface treatment | Untreated |
| Connections - terminals | Screw terminal |
| Clamping connection capacity | 1 x 1.5...4 x 1.5 mm ² for rigid or stranded cable(s) 3 x 2.5 mm ² for stranded cable(s) 1 x 4 mm ² for stranded cable(s) |
| Height | 23 mm |
| Width | 23 mm |
| Depth | 32 mm |
| Net weight | 0.016 kg |

Environment

| | |
|---------------------------------------|-----------|
| Ambient air temperature for operation | 0...45 °C |
| Relative humidity | 10...95 % |
| Product certifications | RCM |

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 2.2 cm |
| Package 1 Width | 2.2 cm |
| Package 1 Length | 2.4 cm |
| Package 1 Weight | 16.98 g |

