

Product data sheet

Characteristics

PDLP391-15G

Pro Series, switched socket, switch & socket, vert, 15 A



Main

Range	Pro Series
Product or component type	Switched socket
Device presentation	Mechanism with fixing frame
Outlet poles configuration	2P + E with shutter
Outlet standard	Australian

Complementary

Device mounting	Flush
Number of power socket outlets	1
Number of rocker	1
Range compatibility	Pro Series
Outlet standard description	With earthing contact
Outlet standard deviation	Australian/New Zealand
Ground lug position	Straight 180° position
Fixing mode	By screws
Installation direction	Vertical
Surface treatment	Untreated
Type of packing	Polybag
Quantity per set	Set of 10
Sale per indivisible quantity	1
Rated current	15 A at 250 V AC 50 Hz
Connections - terminals	3 screw terminals
Screwdriver shape	Square drive no 1 (SQ1) Philips No 2
Clamping connection capacity	1 x 2.5...4 x 2.5 mm ² for rigid or stranded cable(s) 3 x 4 mm ² for rigid or stranded cable(s)
Wire stripping length	16 mm
Material	PC (polycarbonate): fixing frame PP (polypropylene) POM (polyoxymethylene): shutter
Height	112 mm
Width	72 mm
Depth	30 mm
Net weight	0.078 kg

Environment

Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %
Standards	AS/NZ 3112
Product certifications	RCM

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.6 cm
Package 1 Width	7.2 cm
Package 1 Length	11.2 cm
Package 1 Weight	80.56 g

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------