


## Product data sheet

### Characteristics

# PDLP395C-BK

## Pro Series, Cover Plate Double Switched Socket, 10A Horizontal, Black



### Main

Range	Pro Series
Product or component type	Cover frame
Colour tint	Black (BK)
Type of packing	Polybag

### Complementary

Range compatibility	Pro Series switched socket
Product destination	Switched socket
Number of rocker	2
Number of power socket outlets	2
[In] rated current	10 A
Installation direction	Horizontal
Fixing mode	Clip-on
Surface finish	Glossy
Material	PC (polycarbonate): window ABS (acrylonitrile butadiene-styrene): skin
Height	78 mm
Width	116 mm
Depth	9 mm
Net weight	0.018 kg

### Environment

Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.9 cm
Package 1 Width	7.8 cm
Package 1 Length	11.6 cm
Package 1 Weight	19.94 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations