

## Product data sheet

### Characteristics

# PDLP395H4-XW

## Pro Series, Quad Switched Socket, 10A Horizontal, White



### Main

Range	Pro Series
Product or component type	Switched socket
Device presentation	Complete product
Outlet poles configuration	2P + E with shutter
Outlet standard	Australian

### Complementary

Device mounting	Flush
Number of power socket outlets	4
Number of rocker	4
Range compatibility	Pro Series
Outlet standard description	With earthing contact
Outlet standard	Australian/New Zealand
Ground lug position	Straight 180° position
Fixing mode	By screws
Installation direction	Horizontal
Surface finish	Glossy
Surface treatment	Untreated
Type of packing	Polybag
Quantity per set	Set of 10
Sale per indivisible quantity	1
Rated current	10 A at 250 V AC 50 Hz
Connections - terminals	3 screw terminals
Screwdriver shape	Square drive no 1 (SQ1) Philips No 2
Clamping connection capacity	1 x 2.5...4 x 2.5 mm <sup>2</sup> for rigid or stranded cable(s) 3 x 4 mm <sup>2</sup> for rigid or stranded cable(s)
Wire stripping length	16 mm
Material	PC (polycarbonate): fixing frame PP (polypropylene) POM (polyoxymethylene): shutter PC (polycarbonate): window ABS (acrylonitrile butadiene-styrene): infill piece ABS (acrylonitrile butadiene-styrene): skin
Height	78 mm
Width	212 mm
Depth	38 mm
Net weight	0.216 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Environment

Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %
Standards	AS/NZ 3112
Product certifications	RCM
IK degree of protection	IK08

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.6 cm
Package 1 Width	7.2 cm
Package 1 Length	20.5 cm
Package 1 Weight	161.17 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations