


Product data sheet

Characteristics

PDLP395PI-XW

Pro Series, switched socket, 2 switch & 2 socket, power indic, hori, 10 A, White



Main

Range	Pro Series
Product or component type	Switched socket
Device presentation	Complete product
Outlet poles configuration	2P + E with shutter
Outlet standard	Australian

Complementary

Device mounting	Flush
Number of power socket outlets	2
Number of rocker	2
Range compatibility	Pro Series
Outlet standard description	With earthing contact
Outlet standard	Australian/New Zealand
Ground lug position	Straight 180° position
Fixing mode	By screws
Installation direction	Horizontal
Local signalling	Power status (green) for power supply
Surface finish	Glossy
Surface treatment	Untreated
Type of packing	Polybag
Quantity per set	Set of 10
Sale per indivisible quantity	1
Rated current	10 A at 250 V AC 50 Hz
Connections - terminals	3 screw terminals
Screwdriver shape	Square drive no 1 (SQ1) Phillips No 2
Clamping connection capacity	1 x 2.5...4 x 2.5 mm ² for rigid or stranded cable(s) 3 x 4 mm ² for rigid or stranded cable(s)
Wire stripping length	16 mm
Material	PC (polycarbonate): fixing frame PP (polypropylene) POM (polyoxymethylene): shutter PC (polycarbonate): window ABS (acrylonitrile butadiene-styrene): infill piece ABS (acrylonitrile butadiene-styrene): skin
Height	78 mm
Width	116 mm
Depth	38 mm
Net weight	0.094 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %
Standards	AS/NZ 3112
Product certifications	RCM
IK degree of protection	IK08

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.8 cm
Package 1 Width	7.8 cm
Package 1 Length	11.6 cm
Package 1 Weight	111.11 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations