

Product data sheet

Characteristics

PDLS132FBW

1-Way Enclosed Main Switch; 32A, 240VAC, 50 Hz, 1-Pole, White



Main

Range of product	S Series
Product or component type	Switch
Material	PC (polycarbonate)
Surface finish	Gloss

Complementary

Installation direction	Vertical
Width	28.4 mm
Height	70 mm
Depth	51 mm
Rated current	32 A
[Ue] rated operational voltage	250 V
Network frequency	50 Hz
Number of poles	1
Mounting mode	Surface mounted
IP degree of protection	IP66
Cable cross section	25 mm ²
Quantity per set	Set of 10
Type of packing	Carton

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.1 cm
Package 1 Width	3 cm
Package 1 Length	4.6 cm
Package 1 Weight	83.5 g

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
-------------------	--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.