

Product data sheet

Characteristics

PDLS220EM

1-Way Enclosed Main Switch; 20A, 415VAC, 50 Hz, 2P, White

Main

Range of product	S Series
Product or component type	Switch
Material	PC (polycarbonate)
Colour tint	White
Surface finish	Gloss

Complementary

Installation direction	Vertical
Width	82 mm
Height	165 mm
Depth	81 mm
Rated current	20 A
[Ue] rated operational voltage	415 V
Network frequency	50 Hz
Motor M-rating AS3133	M125
Number of poles	2
Mounting mode	Surface mounted
IP degree of protection	IP66
Cable cross section	16 mm ²
Quantity per set	Set of 1
Type of packing	Carton

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.9 cm
Package 1 Width	8.3 cm
Package 1 Length	16.7 cm
Package 1 Weight	430 g
Unit Type of Package 2	CAR
Number of Units in Package 2	10
Package 2 Height	18.8 cm
Package 2 Width	17.7 cm
Package 2 Length	41.7 cm
Package 2 Weight	4300.0 g
Unit Type of Package 3	PAL
Number of Units in Package 3	480
Package 3 Height	112.8 cm
Package 3 Width	70.8 cm

Package 3 Length	83.4 cm
Package 3 Weight	206400.0 g

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------
