

Product data sheet

Characteristics

PDLS392XC-SH

PDL Iconic, cover frame, 3 switches & 2 sockets, 10 A, vertical, silver shadow



Main

Range	PDL Iconic
Aesthetic name	Iconic Styl
Product or component type	Cover frame
Colour tint	Cover frame: silver shadow (SH)
Type of packing	Polybag
Quantity per set	Set of 10

Complementary

Range compatibility	PDL Iconic switched socket
Product destination	Switched socket
Device mounting	Flush
Number of rocker	3
Number of power socket outlets	2
[In] rated current	10 A
Installation direction	Vertical
Fixing mode	Clip-on
Surface finish	Satin
Surface treatment	Metallic
Material	PC (polycarbonate): window ABS (acrylonitrile butadiene-styrene): skin Aluminium
Height	126.0 mm
Width	82 mm
Depth	8.5 mm
Net weight	0.03 kg

Environment

Ambient air temperature for storage	0...45 °C
Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1 cm
Package 1 Width	8.17 cm
Package 1 Length	12.62 cm
Package 1 Weight	52 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations