

Product data sheet

Characteristics

PDLS392XC-SH

PDL Iconic, cover frame, 3 switches & 2 sockets, 10 A, vertical, silver shadow



Main

Range	PDL Iconic
Aesthetic name	Iconic Styl
Product or component type	Cover frame
Colour tint	Cover frame: silver shadow (SH)
Type of packing	Polybag
Quantity per set	Set of 10

Complementary

Range compatibility	Switched socket
Product destination	Switched socket
Device mounting	Flush
Number of rocker	3
Number of power socket outlets	2
[In] rated current	10 A
Installation direction	Vertical
Fixing mode	Clip-on
Surface finish	Satin
Surface treatment	Metallic
Material	PC (polycarbonate): window ABS (acrylonitrile butadiene-styrene): skin Aluminium
Height	126.0 mm
Width	82 mm
Depth	8.5 mm
Net weight	0.03 kg

Environment

Ambient air temperature for storage	0...45 °C
Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.