

Product data sheet

Characteristics

PDLS882WH

2-Way Switch; 16A/16AX, 250VAC, 50 Hz, 2-Gang, 1-Pole, White



Main

Range of product	Strato 800 Series
Range	Strato 800 Series
Product or component type	Switch module
Control type	Rocker
Type of packing	Carton
Colour tint	White



Complementary

Number of ways	2 ways
Material	Metal and plastic
Surface finish	Brushed finish
Width	124 mm
Height	85 mm
Depth	7.5 mm
Rated current	16 AX 16 A
[Ue] rated operational voltage	250 V
Network frequency	50 Hz
Network number of phases	1 phase
Number of gangs	2 gangs
Mounting mode	Surface mounted
Fixing center	84 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5 cm
Package 1 Width	8.5 cm
Package 1 Length	12.5 cm
Package 1 Weight	0.142 kg

Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	 RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Circularity Profile	End Of Life Information
