

Product data sheet

Characteristics

PDLS894WH

Modena and Strato 800 Series, Fully Assembled Switch Socket Outlet, Single, 10A



Main

Range of product	Strato 800 Series
Product or component type	Switched socket
Control type	Rocker
Colour tint	White
Quantity per set	Set of 1
Type of packing	Carton

Complementary

Material	Metal and plastic
Surface finish	Brushed finish
Surface treatment	Aluminium-coated
Width	124 mm
Height	85 mm
Depth	7.5 mm
Rated current	10 A
[Ue] rated operational voltage	230/240 V
Network frequency	50 Hz
Number of gangs	1 gang
Network number of phases	1 phase
Mounting mode	Surface mounted
Fixing center	84 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	8.5 cm
Package 1 Length	12.5 cm
Package 1 Weight	0.137 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration

RoHS exemption information

 Yes

Circularity Profile

 End Of Life Information
