

# Product data sheet

## Characteristics

# PDLS895WH

## Fully Assembled Double Switch Socket Outlet; 10A,White

### Main

Range of product	Strato 800 Series
Product or component type	Switched socket
Colour tint	White
Quantity per set	Set of 1
Type of packing	Carton

### Complementary

Material	Metal and plastic
Surface finish	Brushed finish
Surface treatment	Aluminium-coated
Width	124 mm
Height	85 mm
Depth	7.5 mm
Rated current	10 A
[Ue] rated operational voltage	230/240 V
Network frequency	50 Hz
Number of gangs	2 gangs
Network number of phases	1 phase
Mounting mode	Surface mounted
Fixing center	84 mm

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	8.5 cm
Package 1 Length	12.5 cm
Package 1 Weight	0.146 kg

### Offer Sustainability

REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Circularity Profile	<a href="#">End Of Life Information</a>