

Product data sheet

Characteristics

PDLWSO310LEGY

WP Series, Switched Socket, 10A Less Enclosure, Grey



Main

Range of product	WP Series
Product or component type	Switched socket
Control type	Rocker
Material	PC (polycarbonate)
Colour tint	Light grey

Complementary

Surface finish	Gloss
Installation direction	Horizontal
Width	84 mm
Height	84 mm
Depth	85 mm
Rated current	10 A
[Ue] rated operational voltage	230/240 V
Network frequency	50 Hz
Number of gangs	1 gang
Mounting mode	Surface mounted
IP degree of protection	IP55
Type of packing	Carton

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5 cm
Package 1 Width	8.5 cm
Package 1 Length	8.5 cm
Package 1 Weight	0.096 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	6
Package 2 Height	85 cm
Package 2 Width	45 cm
Package 2 Length	84 cm
Package 2 Weight	1500 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information