

## Product data sheet

### Characteristics

# PDLWSO315LEGY

## Weather Protected Single Switch Socket Outlet; 15A, 1-Gang, Light Grey



### Main

Range of product	WP Series
Product or component type	Switched socket
Control type	Rocker
Material	PC (polycarbonate)
Colour tint	Light grey






### Complementary

Surface finish	Gloss
Installation direction	Horizontal
Width	84 mm
Height	84 mm
Depth	85 mm
Rated current	15 A
[Ue] rated operational voltage	230/240 V
Network frequency	50 Hz
Number of gangs	1 gang
Mounting mode	Surface mounted
IP degree of protection	IP55
Type of packing	Carton

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	8.5 cm
Package 1 Length	8.5 cm
Package 1 Weight	0.095 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	6
Package 2 Height	85 cm
Package 2 Width	45 cm
Package 2 Length	84 cm
Package 2 Weight	1500 g
Package 3 Height	110 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#"> REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#"> EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#"> China RoHS Declaration</a>
RoHS exemption information	<a href="#"> Yes</a>
Environmental Disclosure	<a href="#"> Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations