

Product data sheet

Characteristics

S31LCDA

Standard Series - LV Power Factor Correction Module - 500W



Main

Range	Standard Series
Product or component type	Power factor controller
Device application	Load control
Range compatibility	Clipsal dimmer

Complementary

Rated voltage	240 V AC 50 Hz
Rated operational power in W	500 W at 200...240 V
Ambient air temperature for operation	0...65 °C
Relative humidity	5...95 %
Width	30 mm
Height	20 mm
Depth	10 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.5 cm
Package 1 Width	3.5 cm
Package 1 Length	10 cm
Package 1 Weight	20 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Unit Type of Package 3	CAR
Number of Units in Package 3	100

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information