

Product data sheet

Characteristics

SEA9TB1001

Terminal block, Acti9, 100A, 1P

Main

Range	Acti9
Product or component type	Terminal block
Device application	Connection

Complementary

Range compatibility	Acti 9 Acti9 DB TNA chassis Acti 9 Acti9 DB PEV chassis
[Ie] rated operational current	125 A
[Ui] rated insulation voltage	500 V
Poles description	1P
[Uimp] rated impulse withstand voltage	6 kV
Width	18 mm
Cable stiffness	Flexible 35 mm ² Solid 50 mm ²
Ambient air temperature for storage	-40...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.000 cm
Package 1 Width	7.000 cm
Package 1 Length	9.000 cm
Package 1 Weight	77.500 g
Unit Type of Package 2	S02
Number of Units in Package 2	52
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	4.290 kg
Unit Type of Package 3	P12
Number of Units in Package 3	832
Package 3 Height	45.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	80.640 kg

Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	No
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Halogen content performance	Halogen free plastic parts product
Take-back	No
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	135