

# Product data sheet

## Characteristics

# VDIM189412

## Actassi 19-C Side Cable Management 2U

### Vertical Ring



#### Main

Range	Actassi
Product	Vertical ring
Product destination	Rack 800 mm wide
Additional features	Openable

#### Complementary

Number of rack unit	2U
Maximum capacity	48
Material	Metal sheet: DC01 1.2 mm Plastic part: PA66 GF20 Plastic part: PC
Colour	Dark grey (RAL 7016) Light grey (RAL 7035)
Width	0.11 M 110 mm
Height	0.40 M 40 mm
Depth	100 Mm 0.10 m

#### Environment

Temperature range	-10...55 °C -10...55 °C
-------------------	----------------------------

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	142.9 g
Package 1 Height	4.0 cm
Package 1 width	11.0 cm
Package 1 Length	14.0 cm
Unit Type of Package 2	S04
Number of Units in Package 2	80
Package 2 Weight	12.206 kg
Package 2 Height	30.0 cm
Package 2 width	40.0 cm
Package 2 Length	60.0 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------