

Product data sheet

Characteristics

VDIM189412

Actassi 19-C Side Cable Management 2U Vertical Ring



Main

Range	Actassi
Product	Vertical ring
Product destination	Rack 800 mm wide
Additional features	Openable

Complementary

Number of rack unit	2U
Maximum capacity	48
Material	Metal sheet: DC01 1.2 mm Plastic part: PA66 GF20 Plastic part: PC
Colour	Dark grey (RAL 7016) Light grey (RAL 7035)
Width	0.11 M 110 mm
Height	0.40 M 40 mm
Depth	100 Mm 0.10 m

Environment

Temperature range	-10...55 °C -10...55 °C
-------------------	----------------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.000 cm
Package 1 Width	11.000 cm
Package 1 Length	14.000 cm
Package 1 Weight	142.900 g
Unit Type of Package 2	S04
Number of Units in Package 2	80
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	12.206 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------