

Product data sheet

Characteristics

WMB463

Metal Clad, Socket Outlet 1 Gang, 63A, 500V,
4 Round Sockets



Main

Range of product	Wilco
Product brand	Clipsal

Complementary

Device mounting	Surface
Mounting mode	External mounting
[In] rated current	63 A
[Ue] rated operational voltage	500 V 50/60 Hz conforming to EN 60309-2
Voltage colour	Black
Duration	7 h
Material	Cast aluminium
Socket number	1
Socket-outlet type	A3
Depth	182 mm
Width	115 mm
Height	183 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11 cm
Package 1 Width	18.4 cm
Package 1 Length	18.4 cm
Package 1 Weight	3150.8 g
Unit Type of Package 2	CAR
Number of Units in Package 2	2
Package 2 Height	13.2 cm
Package 2 Width	20 cm
Package 2 Length	39.5 cm
Package 2 Weight	6.498 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations