



### Main

Range of product	Weathershield
Product or component type	Push-button
Colour	Resistant grey
Product brand	Clipsal
Device presentation	Basic element with full cover plate

### Complementary

Colour code	RG
Actuator	Push-button
Contacts type and composition	1 NO for contacts close 1 NC for contacts open
Local signalling	Without light indicator
Fixing mode	By screws
Material	Plastic
Marking location	Marking on surface
[Ue] rated operational voltage	440 V AC
Inrush current	10 A
Marking	START-STOP
Mounting position	Horizontal

### Environment

IP degree of protection	IP66
-------------------------	------

### Packing Units

Package 1 Weight	223.800 g
Package 1 Height	88.000 mm
Package 1 width	88.000 mm
Package 1 Length	88.000 mm

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>