

Product data sheet

Characteristics

WSC227/2/15-RG

SWITCHED SOCKET TWIN WEATHER PROTECTED 15A 250V



Main

Range of product	Weathershield
Product brand	Clipsal
Colour	Resistant grey

Complementary

Control type	Sliding type ON/OFF button
Number of gangs	2 gangs
Pin number	3
Number of power socket outlets	2
Fixing mode	By screws
Local signalling	Without light indicator
Mounting position	Horizontal
Material	Plastic
[Ue] rated operational voltage	250 V AC
[In] rated current	15 A
Length	115 mm
Width	85 mm
Fixing center	84 mm

Environment

IP degree of protection	IP53
Standards	AS/NZS 3112:approval number S/1

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	274.0 g
Package 1 Height	8.3 cm
Package 1 width	8.6 cm
Package 1 Length	11.8 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile