

# Product data sheet

## Characteristics

# WSCF227/2-RG

Socket, Weathershield, Flush, Twin, 10A, 250VAC, IP54

### Main

Range of product	Weathershield
Product brand	Clipsal

### Complementary

Control type	Sliding type ON/OFF button
Number of gangs	2 gangs
Pin number	3
Number Of Outlets	2
Mounting Type	By screws
Local signalling	Without light indicator
Installation Orientation	Horizontal
Material	Plastic
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	55 mm
Length	115 mm
Width	82 mm
Mounting Centers	84 mm

### Environment

IP degree of protection	IP54
Standards	AS/NZS 3112:approval number S/1

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.4 cm
Package 1 Width	8.8 cm
Package 1 Length	12.2 cm
Package 1 Weight	220.0 g

## Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	Yes
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
Take-back	No
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	4