

# Техническа спецификация за продукт Характеристики

## НМІРЕРХСZLSRZZ

Лиценз - Време за изграждане -  
Професионален -3 месеца, EcoStruxure  
Operator Terminal Expert

### Заглавна страница

Гама на продукта	EcoStruxure Operator Terminal Expert
Тип продукт или компонент	Лиценз
Формат	Digital
Тип софтуер	Professional
Тип лиценз	Node locked license
Вариант	Buildtime
Версия на софтуера	V3.5
Operating system requirement	Windows 10 64 bit
Изисквания на системата	8 GB RAM 30 GB hard-drive space
Език на потребителя	Английски Италиански Китайски Испански Френски Немски Португалски Korean

## Допълнителни устройства

License category	Temporary
Протокол на комуникационния порт	CANopen slave Couzet Automation millenium 3 FBD Emerson Industrial Automation Modbus SIO master Control Techniques Modbus SIO master Emerson Process Management ROC Plus Ethernet Emerson Process Management ROC SIO HTTP IPsec Mitsubishi A series Ethernet Mitsubishi FX series CPU direct Mitsubishi FX series Ethernet Mitsubishi iQ-R/F series Ethernet SLMP client Mitsubishi Q series CPU direct Mitsubishi Q series QnU CPU Ethernet Mitsubishi Q/QnA series serial Modbus Organization Modbus SIO ASCII master Modbus Organization Modbus SIO master Modbus Organization Modbus SIO slave Modbus Organization Modbus TCP главен Modbus Organization Modbus TCP slave Omron CS/CJ/CP series host link Omron CS/CJ/CP/NX series Ethernet Omron CS/CJ/NJ/NX series Ethernet/IP OPC UA server Profibus DP slave Rockwell Automation EtherNet/IP Rockwell Automation DF1 Rockwell Automation DH485 Schneider Electric Modbus SIO master Schneider Electric Modbus TCP главен Schneider Electric Modbus TCP главен via USB Schneider Electric Machine expert network Schneider Electric PacDrive Schneider Electric Uni-Telway Schneider Electric Zelio Logic Siemens Simatic S7 Ethernet Siemens Simatic S7 MPI direct Siemens TIA portal Ethernet
Предишна версия на софтуера	V3.4
Функция на софтуера	Professional screen design Simulation Alarms and events Blocky script Convertors Dockable windows interface environment Export with CSV and tab delimiter Import with CSV and tab format Data and operation logging Multi language development Multi language tables Object binding and properties Target binding and properties Project transfer (Ethernet, filesystem, USB cable) Recipes Screens (contents and folders) Security (levels, project, users) Project and application settings System keypad Text script Color themes Variable (arrays, binding, properties, structures) Online and integrated help system OPC UA Server Web server API
Съвместимост на гамата	Harmony GTU Harmony GTUX Harmony ST6 Harmony STM6 Harmony STO7 Harmony iPC
Hosting option	On-premise
License duration	3 month(s)
License size	Single (1 station)

Processor requirement	Intel core i3 8th generation Intel core i5 8th generation
Разделителна способност на диспея	1280 x 720 pixels HD

### Опаковъчни единици

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1 cm
Package 1 Width	1 cm
Package 1 Length	1 cm
Package 1 Weight	1 g